CLOSED CIRCUIT COOLER	FVADCO 1	INC. evapco	DWG.# WX409183608P-DRA-ST REV
MODEL# ESW4 9-34J18-LP SCALE NTS	LVAPCO, I		DATE: 11/5/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT USE	(2) 4" [100] BFW	FACE B LAN VIEW (2) 4" [100] BFW FLUID OUT	FACE D CE A
FOR PRE-FABRICATION OF CONNECTING PIPIN 9. COIL CONNECTIONS LOCATED ON FACES B AN	D D * 2'-8"	* 2'-2 3/8" [670] -10 3/4" [883] [M) ACCESS DOOR	1'-0 7/8" [327] [ACCESS] DOOR 8'-3 1/4" [2522]
2" [50] MPT — MAKE-UP — 2" [50] MPT — DRAIN — O	3" [80] MPT OVERFLOW	/2" [15] FPT VENT 0 0 0 0 0	9'-6 1/8" [2900]
3 3/8" [86] 4 1/4" [107] 5 1/4" [132] 8'-5 1/2" [2578] FACE B	2'-5 5/8" [752]		-0"
SHIPPING WEIGHT 20350 lbs+ [9235] kg+ OPER WEI	28990 lbs+ [13150] kg+	HEAVIEST SECTION 13580 lbs+ [6160] kg+	NO. OF SHIPPING SECTIONS 2 DRAWN BY: AWT