

UNIT	CLOSED CIRCUIT COOLER
MODEL #	ESW4 9-43J6-LP

**EVAPCO, INC.**




DWG. # WX409064806P-DRA-ST

REV -  
SERIAL #  
DATE: 2/8/2026


NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS COIL SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
- \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

FACE C




FACE B  
PLAN VIEW



FACE B

FACE D

FACE A



FACE A

SHIPPING  
WEIGHT

7330 lbs+ [3325] kg+

OPERATING  
WEIGHT

10210 lbs+ [4635] kg+

HEAVIEST SECTION  
WEIGHT

4770 lbs+ [2165] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT