UNIT	COOLING TOW		EVAPCO, INC. Evapeo SER			NG. # T4142448-DRA-ST	REV.
MODEL #	AT 114-4K24	SCALE NTS	EVAP	CO, INC.	SE	RIAL #	DATE _{11/11/2025}
2. HÉAVIE 3. MPT DE FPT DE BFW DI GVD DE FLG DE PE DEN 4. +UNIT V ACCES 5. MAKE-U 20 psi M 6. 3/4" [19 REFER DRAWII 7. DIMENS	N MOTOR LOCATION ST SECTION IS UPPER SENOTES MALE PIPE THRE NOTES FEMALE PIPE THE ENOTES BEVELED FOR VENOTES GROOVED NOTES FLANGE IOTES PLAIN END VEIGHT DOES NOT INCLISORIES (SEE ACCESSOF) JP WATER PRESSURE IIN [137 KPa], 50 psi MAX [MM] DIA. MOUNTING HOL TO RECOMMENDED STE NG SIONS LISTED AS FOLLOW GLISH FT-IN TRIC] [mm]	EAD READ /ELDING JDE LY DRAWINGS) 344 kPa] ES. EL SUPPORT		FACE B PLAN VIEW		ACCESS DOOR	ACE D
			7" [178]	1'-5 1/4" [438]			
			11'-2 1/4" [3410]				
		_ -			11'-10 1/2"	14" [350] BFW/GVD INLET	
			8'-3 1/4" [2521]	13'-3 3/4" [4058]			
			<u>, , , , , , , , , , , , , , , , , , , </u>	2'-2" [660] 1'-5 3/8" [229] —	4" [100] FPT	14" [350] BFW/GVD OUTLET	
	13'-11 1/4' [4248] FACE B		3/8" [9]	9" [229]	11'-10 1/2"	-9" -39] 	
SHIPPING WEIGHT	18950 lbs+ [8	600] kg+	OPERATING WEIGHT 34800 lbs+ [15	790] kg+ HEAVIEST SECTION WEIGHT	12680 lbs+ [5755] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: MER