UNIT COOLING TOWER				A DCO T	NC PV	apco °	DWG. #	T4285260-DRA-ST	REV.
10DEL #	AT 428-5N52	SCALE NTS	EV	APCO, I	NC.	<b>1</b>	SERIAL #		DATE <sub>12/14/2025</sub>
2. HEAVI 3. MPT D FPT D BFW D GVD D FLG D PE DE 4. +UNIT ACCE: 5. MAKE: 20 psi 6. 3/4" [1 REFEE DRAW 7. DIMEN [MI 8. PAN F EVAPC BY OT 9. PAN E	NSIONS LISTED AS FOLLOW IGLISH FT-IN ETRIC] [mm] FLUME BOX EQUALIZERS SU CO. PAN EQUALIZER PIPING	DE DE DRAWINGS)  44 kPa] S. L SUPPORT  S:  IPPLIED BY IS SUPPLIED		FACE B		(8) ACCESS DOOR			FACE D
(4) 4	OUTLET 1" [100] MPT -	11'-6" 3505 ] -1 1/4" 3994 ] -5 1/2" 4102 ] -6 1/2" 4128 ] 11 1/4"	1'-3 1/4" [ 387 ]  6'-11 5/8" [ 22'-2'-2'' [ 660 ]	7" [178]  12'-1/4" [3664]  2" [51]  10'-3 1/4" [3131]	25'-9' [ 7849	9 1/8" [ 232 ] 1 3/8" [ 35 ]	(4) 12" BFW/GV (SEE NO	D EQUALIZER	2" [51]
-	28'-3 5/8" [ 8626 ] <b>FACE B</b>	-		[ 38 ]		[ 16789 ] FACE A	1		
SHIPPING 99120 lbs+ [44965] kg+ WEIGHT		OPERATING 166 WEIGHT	6440 lbs+ [75500] kg+	HEAVIEST SECTION WEIGHT	18140 lbs+ [8230] kg+	NO. OF SHIF	PPING SECTIONS 8	DRAWN BY: MER	