

| | | | | | | | | | | | | | | | | | |
|--|--|------------------------|--|---|-------------------------|------------------------|----------------|-------------------------|--|-----------------------|--|--------------------------|--|---|--|---------------|--|
| UNIT | | CONDENSER | | <div>EVAPCO, INC.</div> <div>evapco</div> | DWG. # WB3171412-DRD-ST | | REV. - | | | | | | | | | | |
| MODEL # eco-ATC-988A | | SCALE NTS | | | SERIAL # | | DATE 8/17/2025 | | | | | | | | | | |
| <div>NOTES:</div> <div>1. (M)- FAN MOTOR LOCATION</div> <div>2. HEAVIEST SECTION IS UPPER SECTION</div> <div>3. MPT DENOTES MALE PIPE THREAD</div> <div> FPT DENOTES FEMALE PIPE THREAD</div> <div> BFW DENOTES BEVELED FOR WELDING</div> <div> GVD DENOTES GROOVED</div> <div> FLG DENOTES FLANGE</div> <div> PE DENOTES PLAIN END</div> <div>4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)</div> <div>5. MAKE-UP WATER PRESSURE</div> <div> 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]</div> <div>6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING</div> <div>7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.</div> <div>8. DIMENSIONS LISTED AS FOLLOWS:</div> <div> ENGLISH FT-IN</div> <div> METRIC [mm]</div> | | | | | | | | | | | | | | | | | |
| <div>PLAN VIEW</div> <div>FACE B</div> <div>FACE C</div> <div>FACE D</div> <div>FACE A</div> | | | | | <div>FACE A</div> | | | | | | | | | | | | |
| <div>FACE B</div> | | | | | <div>FACE A</div> | | | | | | | | | | | | |
| SHIPPING WEIGHT | | 42880 lbs+ [19455] kg+ | | OPERATING WEIGHT | | 53160 lbs+ [24115] kg+ | | HEAVIEST SECTION WEIGHT | | 19360 lbs+ [8785] kg+ | | NO. OF SHIPPING SECTIONS | | 4 | | DRAWN BY: SLR | |