| UNIT    | CONDENSER    |           |
|---------|--------------|-----------|
| MODEL # | eco-ATC-330A | SCALE NTS |


EVAPCO, INC. Evapco



DWG. # REV. EG091406-DRC-ST DATE<sub>10/29/2025</sub> SERIAL #


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]






**FACE D** 

**FACE A** 





DRAWN BY: JLG NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 13500 lbs+ [6125] kg+ 18200 lbs+ [8260] kg+ 11420 lbs+ [5185] kg+ WEIGHT WEIGHT WEIGHT