

UNIT	CONDENSER
MODEL #	ATC-1026E

EVAPCO, INC.




DWG. # C4122410-DRA-ST

REV -
SERIAL #
DATE: 2/4/2026

NOTES

1. (M)- FAN MOTOR LOCATION
2. MPT DENOTES MALE PIPE THREAD
3. FPT DENOTES FEMALE PIPE THREAD
4. BFW DENOTES BEVELED FOR WELDING
5. GVD DENOTES GROOVED
6. FLG DENOTES FLANGE
7. PE DENOTES PLAIN END
8. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
9. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
10. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
11. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
12. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



SHIPPING
WEIGHT

38540 lbs+ [17485] kg+

OPERATING
WEIGHT

51580 lbs+ [23400] kg+

HEAVIEST SECTION
WEIGHT

31920 lbs+ [14480] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG