LINUT			DWO #	I pry
CONDENSER	- FVADC	O, INC. Evaped	DWG.# C4122408-DRA-ST	REV -
MODEL# ATC-894E N7	TS LVAPC	O, little	SERIAL #	DATE: 11/1/2025
NOTES 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWIN 4. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 5. *-APPROXIMATE DIMENSIONS DO NOT US FOR PRE-FABRICATION OF CONNECTING PIPING 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFEI RECOMMENDED STEEL SUPPORT DRAWIN 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]	E R TO	FACE B PLAN VIEW	FACE A	FACE D
3'-2 3/4"[984] * 2" [50] MPT	5'-2" [1575] 16'-0 1/2" [4889] 6" [152] * 6'-2 3/8" [1889]	1'-3 1/4" [387] (M) AC DO 2'-10 3/8" [873]	OR	ACCESS DOOR
FACE B				
SHIPPING WEIGHT 34080 lbs+ [15460] kg+	OPERATING WEIGHT 46930 lbs+ [21290] kg-	+ HEAVIEST SECTION 27460 lbs+ [12460] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: JLG