

UNIT	CONDENSER		EVAPCO, INC. 	DWG. #	CW4C073612-DRA-ST	REV.	-
MODEL #	eco-ATC-989A	SCALE NTS		SERIAL #	DATE 1/22/2026		

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]




DWG. # CW14C032612.DWG ST

REV.


SERIAL #

DATE 1/22/2026

FACE B PLAN VIEW



FACE B



FACE A

SHIPPING WEIGHT 64860 lbs+ [29425] kg+ OPERATING WEIGHT 69610 lbs+ [31575] kg+ HEAVIEST SECTION WEIGHT 26630 lbs+ [12080] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: TAM