UNIT	COOLING TOWER	EVADCO 1	NC evapco	DWG. # T4281824-DRA-ST	REV -
MODEL #	AT 228-2L18 SCALE N	EVAPCO, I	NC. evapeo	SERIAL #	DATE: 11/21/2025
2. HÉAVIE 3. MPT DE FPT DE BFW DE GVD DE FLG DE 4. +UNIT V ACCES 5. 3/4" [19] REFER SUPPO 6. DIMENS [MET 7. MAKE-L	N MOTOR LOCATION ST SECTION IS FAN/CASING SECTIONTES MALE PIPE THREAD NOTES FEMALE PIPE THREAD ENOTES BEVELED FOR WELDING ENOTES GROOVED NOTES FLANGE VEIGHT DOES NOT INCLUDE SORIES (SEE ACCESSORY DRAW) MM] DIA. MOUNTING HOLES. TO RECOMMENDED STEEL RT DRAWING SIONS LISTED AS FOLLOWS: LISH FT-IN RIC] [mm] JP WATER PRESSURE IIN [137 kPa], 50 psi MAX [344 kPa]		FACE B PLAN VIEW	CCESS DOOR	CE D
		⊢1'-5 1/4" [438]	7" [178]-]	FACE A	
2 1/8" [54]	(2) 14" [350] BFW/GVD OUTLET (2) 3" [80] FPT OVERFLOW (2) 2" [50] MPT MAKE-UP (2) 3" [80] FPT DRAIN 5 1/8" [130] 28'-3 5/8" [8626]	2 1/8" [54]  2 1/8" [54]  2 1/8" [54]  2 1/8" [54]  2'-2" [660] 13'-2 1/4" [4020] 13'-6 1/8" [4118] 13'-7" [4140] 13'-11 1/4" [4248]	9'-5 1/8" [2873] 9'-6 1/8" [5394] 8'-3 1/4" [2521] 1 3/8" [35]	I3] BFW INLE	4" [350] /GVD T 11'-3 3/4" [3448]
FACE B FACE A					
SHIPPING WEIGHT	30980 lbs+ [14055] kg+	OPERATING WEIGHT 50400 lbs+ [22865] kg+	HEAVIEST SECTION 10420 lbs+ [4730] kg+	NO. OF SHIPPING SECTIONS 4	DRAWN BY: TRS