UNIT	CONDENSER	
MODEL #	eco-ATC-159A	SCALE NTS

EVAPCO, INC. Evapeo

**PLAN VIEW** 



DWG. # REV. WB3041210-DRE-ST DATE<sub>11/27/2025</sub> SERIAL #

**FACE D** 

## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS:


**ENGLISH FT-IN** METRIC [mm]




## **FACE C**



**FACE A** 





**SHIPPING OPERATING** HEAVIEST SECTION 7920 lbs+ [3595] kg+ 10140 lbs+ [4600] kg+ WEIGHT WEIGHT WEIGHT

7100 lbs+ [3225] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: