CONDENSER		<b>EVAPCO</b>	TNC	vapco	DWG. # CEWRTM3610-DRA-ST	REV -
MODEL# PMRC-1382 SCALI	E NTS	EVAPCO			SERIAL#	DATE: 11/27/2025
NOTES:  1. (M)- FAN MOTOR LOCATION.  2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END  3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).  4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.  5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.  6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]  7. *- APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIRES.		FACE B PLAN VIEW		FACE C		FACE D
2'-6 3/8" * [772] 4'-9" *	7			FACE A		
(4) 4" [100]PE R	REFRIG IN 3'-3 1/4"	- " [997] * 6'-6 1/8" [1984]		9/		
DOORS 2"[50] MPT MAKE UP 3"[80] MPT DRAIN 2'-5"[737]	9'-11" [3	15'-0 1/2" [4585] 3023] * 8'-6 3/8" [2600]	(M) + (M)			
1'-8" [508]	3"[80] N OVERF	1'-8"   [508] MPT FLOW		36'-2" [11024]		1'-6 1/4" [464]
[2991] FACE B				FACE A	<u></u>	
SHIPPING WEIGHT 50740 lbs+ [23020] kg+	OPERATING WEIGHT	63030 lbs+ [28590] kg+	HEAVIEST SECTION WEIGHT	18210 lbs+ [8260] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY: JLG