

UNIT	CONDENSER
MODEL #	PMRC-1556

EVAPCO, INC.



DWG. # CEWRTM3612-DRA-ST

REV -


SERIAL #

DATE: 1/15/2026

NOTES:



- (M)- FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,
50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING.

FACE C



FACE B

PLAN VIEW



FACE B

FACE A

SHIPPING
WEIGHT

57600 lbs+ [26130] kg+

OPERATING
WEIGHT

70120 lbs+ [31810] kg+

HEAVIEST SECTION
WEIGHT

21260 lbs+ [9645] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: **JLG**