| NIT CONDENSED | | Te de la constant de | DWG.# | REV |
|--|-------------------------------------|--|--------------------------|----------------------|
| CONDENSER | SCALE | EVAPCO, INC. Evapco | CEWRTM2414-DRA-ST | DATE: |
| PMRC-980 | NTS | | SERVICE# | 11/25/2025 |
| NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD FPT DENOTES GROOVED FLG DENOTES FLANGE FED ENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MII 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METERIC] [mm] 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PI | N, | FACE B PLAN VIEW | FACE A | FACE D |
| 2'-6 3/8" * [772] | 4'-9" * [1448] | | | |
| (4) 4" [100 | O O— REFRIG C | 3'-11 3/4" [1213] * 7'-2 5/8" [2200] | | |
| OVERSIZED ACCESS DOORS 2"[50] MPT MAKE UP 3"[80] MPT DRAIN 2'-5"[737] | | 9'-11" [3023] * 8'-6 3/8" [2600] | | |
| 1'-8" [508] 4 3/4" [121] 3 7/8" [98] 5 1/8" [130] 3'-10 1/2" [1181] | 3"[80] MPT OVERFLOV 9'-9 3/4" | 1'-7 1/8" [486] | _24'-0 7/8" | _ _ 1'-6" [457] |
| [2991] FACE A | | | | |
| SHIPPING 43370 lbs+ [19675] kg+ | OPERATING WEIGHT | 51760 lbs+ [23480] kg+ HEAVIEST SECTION WEIGHT 16720 lbs+ [7585] kg+ | NO. OF SHIPPING SECTIONS | DRAWN BY: JLG |