NIT	CONDENSER		EV/ADCC	TAIC evapeo	DWG.# CEWRTM3606-DRA-ST	REV -
ODEL#	eco-PMRC-1102	SCALE NTS	EVAPUL	O, INC. evapeo	SERIAL#	DATE: 12/14/2025
2. MPT DEN FPT DEN BFW DEN GVD DEN FLG DEN PLG DEN ACCESSO 4. 3/4" [19mm RECOMM 5. MAKE-UP 50 psi [34 6. DIMENSIO ENGLISI [METRIC 7. * - APPRO	N MOTOR LOCATION. NOTES MALE PIPE THREAD NOTES FEMALE PIPE THREAD NOTES BEVELED FOR WELDING NOTES GROOVED NOTES FLANGE OTES PLAIN END VEIGHT DOES NOT INCLUDE SORIES (SEE ACCESSORY DRAWIN nm] DIA. MOUNTING HOLES. REFER MENDED STEEL SUPPORT DRAWIN IP WATER PRESSURE 20 psi [137 KF 44 KPa] MAX. SIONS LISTED AS FOLLOWS: SH FT-IN IC] [mm] ROXIMATE DIMENSIONS DO NOT R PRE-FABRICATION OF CONNECT	INGS). ER TO /ING. kPa] MIN,	FACE B PLAN VIEW	FACE	<u>C</u>	FACE D
		<u>'-</u> 9" *  448]	4! 40 4/4" [565] *	FACE A	<u>A</u>	
DC 2"[50] N MAKE	SIZED (4) 4" [100] PE (4) 4" [100] PE (5) CCESS OORS MPT (E UP 0) MPT DRAIN (121) 5 1/8" [130] 3'-10 1/2" [1181] 9'-9	O REFRIG IN REFRIG OUT	13'-7 1/2" [4153]  13'-7 1/2" [4153]  1-11" [3023] *  1'-8"  [508]	36'-2" [11024]		1'-6 1/4" [464]

HEAVIEST SECTION WEIGHT **FACE A** 

15660 lbs+ [7105] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

JLG

FACE B

45130 lbs+ [20475] kg+

OPERATING WEIGHT

56950 lbs+ [25835] kg+

SHIPPING WEIGHT