

UNIT CLOSED CIRCUIT COOLER
MODEL # ESW4 12-25K18-SF

SCALE NTS

EVAPCO, INC.




DWG. # WX412182410F-DRA-ST

REV -
SERIAL #
DATE: 2/8/2026

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS COIL SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING


FACE C




FACE D

FACE B
PLAN VIEW

FACE A



FACE B



FACE A

SHIPPING
WEIGHT

31560 lbs+ [14320] kg+

OPERATING
WEIGHT

46920 lbs+ [21285] kg+

HEAVIEST SECTION
WEIGHT

24900 lbs+ [11295] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT