UNIT CONDENSER			EVAPCO, INC. Evapeo			NG. # CEWR122412-DRA-ST	REV	-
MODEL# eco-PMRC-964	NTS		EVAPCO, I		S	ERIAL#	DATE:	12/14/2025
NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MII 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING F	IN,		<u>FACE</u> <u>PLAN VI</u>			CE C		FACE D
3'-0 7/8" * [937]	5'-8 5/8" *_ [1743]			175				
O (4) 4" [100] PE O (4) 4" [100] PE		OREFRIG IN	3'-11 3/4" [1213] * 7'-2 5/8"	[2200]				
OVERSIZED ACCESS DOORS 3"[80] MPT 5 1/8" [130] MAKE UP 5 1/8" [130] 2'-5"[737]			15'-9" [4801] 9'-11" [3023] * 8'-6 3/8"	2600])
1'-8" [508]	21] \(2)	3"[80] MPT 'ERFLOW	1'-7 1/8" [48	6]	24'-0 7 [733	//8"		1'-6" [457]
	11'-10 3/8" [3616]	-						
FACE B						FACE A		
SHIPPING WEIGHT 55270 lbs+ [25075] kg+	OPER/ WEI	ATING GHT	65500 lbs+ [29715] kg+	HEAVIEST SECTION WEIGHT	22410 lbs+ [10170] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY:	JLG