UNIT CLOSED CIRCUIT COOLER	EVA DOO	ENG BYGDCO	DWG. # WX41218X4806P-DRA-ST	REV -
MODEL# ESW4 12-43K18X-SP SCALE NTS	EVAPCO, .	INC. evapeo	SERIAL#	DATE: 11/14/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPII 9. COIL CONNECTIONS LOCATED ON FACES B AI 2" [50] MPT DRAIN 2'-4" [711] 4" [107] 5 1/4" [132] 11'-10" [3607] FACE B	(2) 4" [100] BFW FLUID IN NG ND D * 2'-8"	FACE B PLAN VIEW (2) 4" [100] BFW FLUID OUT * 1'-7 1/2" [495] * 4'-7" * 2'-3 3/8" [695] [1397] (2)1/2" [15] FPT VENT 2'-1" [635] [54]	7" [178] 7" [178] 1'-3 (M) 1ACCESS DOOR 10'-3 7	11/14/2023 ACE D 1/4" [387] /8" [3148] 19'-6 5/8" [5961] /4" [2813]
SHIPPING WEIGHT 23430 lbs+ [10630] kg+ OPER WE	35160 lbs+ [15950] kg+	HEAVIEST SECTION 15280 lbs+ [6935] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT