CLOSED CIRCUIT COOLER WX412124810F-DRA-ST EVAPCO, INC. Evapeo MODEL# SERIAL# ESW4 12-45I12-LF 11/17/2025 NTS NOTES: 1. (M)- FAN MOTOR LOCATION **FACE C** 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD _==== FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE **FACE B FACE D** ACCESSORIES (SEE ACCESSORY DRAWINGS) **PLAN VIEW** 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT USE **FACE A** FOR PRE-FABRICATION OF CONNECTING PIPING -1'-3 1/4" [387] * 4'-4 5/8" (M) [1337] **IACCESS** DOOR 10'-3 7/8" [3148] (2) 4" [100] BFW (2) 4" [100] BFW FLUID OUT FLUID IN 2" [50] MPT 20'-6 5/8" [6266] MAKE-UP (2) 1/2" [15] FPT 3" [80] MPT VENT 3" [80] MPT OVERFLOW DRAIN 2'-10 1/2" [876] 10'-2 3/4" [3118] 2'-4" [711]-L* 2'-3 3/8" [695] * 3'-8 5/8" 4 1/4" 4" [101] 1'-7 1/4" 11'-11 3/4" [1135] [107] [489] [3651] 5 1/4" -1'-7 3/8" [492<u>]</u> 4'-9 5/8" [132] [1464] 11'-10" [3607] **FACE A**

FACE B