CLOSED CIRCUIT COOLER	EVADCO :		DWG. # WX41218X4812F-DRA-ST	REV -
MODEL# ESW4 12-46J18X-LF SCALE NTS	1 EVAPCO, .	INC. evapeo	SERIAL#	DATE: 11/20/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIE	(4) 4" [100] BFW FLUID IN	FACE B PLAN VIEW (4) 4" [100] BFW FLUID OUT * 3'-6" [1067]	CE C	ACE D
2" [50] MPT	* 4'-4 5/8" [1337] FACE B & D COIL CONNECTIONS 3" [80] MPT OVERFLOW	(4)1/2" [15] FPT VENT	(M) ACCESS DOOR 10'-3	3 1/4" [387] 3 7/8" [3148] 21'-5 1/8" [6532] 1/4" [3385]
	ERATING 53380 lbs+ [24215] kg+	HEAVIEST SECTION WEIGHT 28700 lbs+ [13020] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT
WEIGHT 307 90 103 + [100 90] kg + W	EIGHT	WEIGHT		/ \ V V I