UNIT CONDENSER		EVADOO 1		vap co	CEWR122406-DRA-ST	REV	-
MODEL# eco-PMRC-1001 SCALE N	rs	EVAPCO, I	.IYC. $ egthanskip$	S	ERIAL#	DATE:	11/26/2025
NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.		FACE E PLAN VIE	- 17188888		CE A		FACE D
3'-0 7/8" * 5'-8 5 [937]	(2) 3"[80] MPT OVERFLOW	1'-10 1/4" [565] * 5'-1 1/8" [13'-7 1/2" [4153] 9'-11" [3023] * 8'-6 3/8" [2	2600]	24'-0 7 [733	(M)-(M) (7/8" 7]		└──1'-6" [457]
SHIPPING WEIGHT 35730 lbs+ [16210] kg+		45380 lbs+ [20585] kg+	HEAVIEST SECTION WEIGHT	12470 lbs+ [5660] kg+		DRAWN BY:	JLG
	WEIGHT		#FLIGHT				