CLOSED CIRCUIT COOLER	EVADOO '	TNC evapeo	DWG.# WX41218X3610F-DRA-ST REV -
MODEL# ESW4 12-35J18X-LF SCALE N	EVAPCO,	INC. evapeo	SERIAL# DATE: 11/9/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWIN 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT US FOR PRE-FABRICATION OF CONNECTING 9. COIL CONNECTIONS LOCATED ON FACES	(4) 4" [100] BFW FLUID IN	FACE B PLAN VIEW (4) 4" [100] BFW FLUID OUT * 2'-10 1/2" [876]	CE C FACE D
	* 4'-4 5/8" * * * * * * * * * * * * * * * * * * *	* 2'-3 3/8" [695] * 3'-8 5/8" [1135]	7" [178] 7" [178] 1-3 1/4" [387] (M) 1 ACCESS DOOR 9'-3 7/8" [2843]
2" [50] MPT MAKE-UP 3" [80] MPT DRAIN 0	3" [80] MPT OVERFLOW	(4)1/2" [15] FPT VENT	19'-9 5/8" [6037] 10'-5 3/4" [3194]
4" [101] 4 1/4" [107] 5 1/4" [132] 11'-10 [3607	1	[635]	2'-3 1/2" 486] [699]
SHIPPING WEIGHT 32840 lbs+ [14900] kg+	OPERATING WEIGHT 48240 lbs+ [21885] kg+	HEAVIEST SECTION 25450 lbs+ [11545] kg+	NO. OF SHIPPING SECTIONS 2 DRAWN BY: AWT