

UNIT CLOSED CIRCUIT COOLER
MODEL # ESW4 12-44L18-SF

SCALE NTS

EVAPCO, INC.




DWG. # WX412184808F-DRA-ST

REV -
SERIAL #
DATE: 2/19/2026

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING



FACE B


FACE B
PLAN VIEW

FACE C



FACE D

FACE A



FACE A

SHIPPING
WEIGHT

29730 lbs+ [13490] kg+

OPERATING
WEIGHT

43880 lbs+ [19905] kg+

HEAVIEST SECTION
WEIGHT

21530 lbs+ [9770] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT