

UNIT	CLOSED CIRCUIT COOLER
MODEL #	ESW4 12-24N18X-LP

SCALE NTS

**EVAPCO, INC.** 

DWG. # WX41218X2408P-DRA-ST


REV -

SERIAL #


DATE: 2/7/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
8. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
9. COIL CONNECTIONS LOCATED ON FACES B AND D




FACE B  
PLAN VIEW




FACE D

FACE A



FACE B & D  
COIL CONNECTIONS



FACE A

FACE B

SHIPPING  
WEIGHT

24760 lbs+ [11235] kg+

OPERATING  
WEIGHT

37290 lbs+ [16915] kg+

HEAVIEST SECTION  
WEIGHT

17680 lbs+ [8020] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT