

UNIT CLOSED CIRCUIT COOLER
MODEL # ESW4 12-35L12-LP


EVAPCO, INC.



DWG. # WX412123610P-DRA-ST

REV -
SERIAL #
DATE: 2/14/2026


- NOTES:
1. (M)- FAN MOTOR LOCATION
 2. HEAVIEST SECTION IS COIL SECTION
 3. MPT DENOTES MALE PIPE THREAD
 - FPT DENOTES FEMALE PIPE THREAD
 - BFW DENOTES BEVELED FOR WELDING
 - GVD DENOTES GROOVED
 - FLG DENOTES FLANGE
 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
 6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
 7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
 8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING




FACE B

FACE B
PLAN VIEW


FACE C



FACE D



FACE A



FACE A

SHIPPING
WEIGHT

18600 lbs+ [8440] kg+

OPERATING
WEIGHT

27400 lbs+ [12430] kg+

HEAVIEST SECTION
WEIGHT

12970 lbs+ [5885] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT