CLOSED CIRCUIT COOLER MODEL# ESW4 12-26I12-LF NTS

EVAPCO, INC. Evapeo



WX412122412F-DRA-ST SERIAL# 10/24/2025

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS COIL SECTION

3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE

4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)


5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING

6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]


8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING **FACE C**

FACE B PLAN VIEW



FACE D

FACE A



SHIPPING 23560 lbs+ [10690] kg+ WEIGHT

OPERATING WEIGHT

34510 lbs+ [15655] kg+

HEAVIEST SECTION WEIGHT

18610 lbs+ [8445] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: