

UNIT	CONDENSER
MODEL #	eco-PMRC-888

**EVAPCO, INC.**



DWG. # CEWR121806-DRA-ST

REV -


SERIAL #

DATE: 2/19/2026

**NOTES:**


1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,  
50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
7. \* - APPROXIMATE DIMENSIONS DO NOT  
USE FOR PRE-FABRICATION OF CONNECTING PIPING.

**FACE C**




**FACE D**

**PLAN VIEW**



**FACE B**



**FACE A**

SHIPPING  
WEIGHT

28190 lbs+ [12790] kg+

OPERATING  
WEIGHT

34990 lbs+ [15875] kg+

HEAVIEST SECTION  
WEIGHT

19170 lbs+ [8700] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG