CLOSED CIRCUIT COOLER	EVADOO :	TNG Tevanco	DWG. # WX41218X2412F-DRA-ST	REV -
MODEL# ESW4 12-26J18X-SF SCALE NTS	EVAPCO,	INC. evapeo	SERIAL#	DATE: 10/28/2025
NOTES:  1. (M)- FAN MOTOR LOCATION  2. HEAVIEST SECTION IS COIL SECTION  3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE  4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS  5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING  6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]  7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]  8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIP  9. COIL CONNECTIONS LOCATED ON FACES B AP	(4) 4" [100] BFW FLUID IN O	FACE B PLAN VIEW  - (4) 4" [100] BFW FLUID OUT  * 3'-6" [1067]	CE A	ACE D
2" [50] MPT	FACE B & D COIL CONNECTIONS  3" [80] MPT OVERFLOW  1'-7 3/8" [492] 4'-9 5/8" [1464]	(4)1/2" [15] FPT VENT	(M)   ACCESS   DOOR   8'-3   11'-1     1   1   1   1   1   1   1   1   1	9]
SHIPPING WEIGHT 35210 lbs+ [15975] kg+ OPE WE	51800 lbs+ [23500] kg+	HEAVIEST SECTION 28610 lbs+ [12980] kg+	NO. OF SHIPPING SECTIONS 2	AWT