EVAPCO, INC. ***BOLLET SAME PORT THE ALL PROPERTY OF THE ALL PROP	UNIT			4	DWG.#	REV
EACE D	CONDENSER		EVADOO TNO evapoo		CEWR121812-DRA-ST	-
1.06, FAM INFORM LOCATION. 2 MOVEMBER PRIVE THE PET WE FINDS 0 OR DECRETE SHOPE IN PET THE PET OR 1 PET AND THE PET TH	MODEL # eco-PMRC-1084 SCALE N	ГS	LVAPCO, I		SERIAL#	
(S) # (1906) PE (S) # (1906) P	1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. *- APPROXIMATE DIMENSIONS DO NOT					FACE D
1'-8" [508] 3"[80] MPT OVERFLOW [5490] 1'-8" [508] 15-0 3/8" [1534] 11'-10 3/8" [3616] FACE B	[937] (1) O(2) 4" [100] PE OVERSIZED ACCESS DOORS 2"[50] MPT MAKE UP 3"[80] MPT	O REFRIG IN	15'-9" [4801]			
	1'-8" [508] 4 3/4" [121] 3 7/8" [98] 5'-0 3/8" [1534] 11'-	0 3/8"		1'-8" [508]	[5490]	
	SHIPPING WEIGHT 42620 lbs+ [19335] kg+	OPERATING WEIGHT	49850 lbs+ [22615] kg+	HEAVIEST SECTION 33470 lbs+ [15185] kg+		DRAWN BY: JLG