UNIT CLO	SED CIRCUIT COOLER	T	<b>EVA DOO</b>	TNIC	Avanco I	DWG. # WX409123612P-DRA-ST	REV _
MODEL#	ESW4 9-36J12-LP	NTS	EVAPCO,	INC.		SERIAL#	DATE: 10/29/2025
2. HÉAVIE 3. MPT DI FPT DE BFW D GVD DI FLG DE 4. +UNIT ACCES 5. 3/4" [19 REFER SUPPO 6. MAKE- 20 psi N 7. DIMEN	N MOTOR LOCATION EST SECTION IS COIL SECTION ENOTES MALE PIPE THREAD ENOTES BEVELED FOR WELDIN ENOTES GROOVED ENOTES FLANGE WEIGHT DOES NOT INCLUDE ESORIES (SEE ACCESSORY DRA MMJ DIA. MOUNTING HOLES. TO RECOMMENDED STEEL DRAWING UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [344 kP SIONS LISTED AS FOLLOWS: BLISH FT-IN TRIC] [mm]	AWINGS)		FACE B PLAN VIEW	FACE C	FACE D	
8. * - APP	ROXIMATE DIMENSIONS DO NO RE-FABRICATION OF CONNECT				FACE A	<sub>[</sub> 1'-0 7/8" [327]	
	(M) * 2'-8" [813]				[,[M],]	(ACCESS) (DOOR) 8'-3 1/4" [2522]	
	4" [100] BFW — FLUID IN 2" [50] MPT — MAKE-UP		4" [100] BFW FLUID OUT  3" [80] MPT OVERFLOW  -* 3'-6" [1067]	1/2" [15] FPT VENT		18'-4 3/	8" [5599] 
	2" [50] MPT DRAIN 2'-3" [686]					10'-1 1/8" [3077]	
	3 3/8" [86] 4 1/4" [107]		* 2'-2 3/8" [670] -1'-6 3/8" [465] 	2'-1 [635	"11'-11 3/4" [3651]		
	5 1/4"	5 1/2" 5 78] CE B	* 2'-10 3/4" [883]		FACE A		
SHIPPING WEIGHT	16970 lbs+ [7700] kg+	OPERATIN WEIGHT	<sup>G</sup> 24230 lbs+ [10995] kg+	HEAVIEST SECTION WEIGHT	13170 lbs+ [5975] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT