

UNIT CLOSED CIRCUIT COOLER
MODEL # ESW4 9-46K12-LP SCALE NTS


EVAPCO, INC.



DWG. # WX409124812P-DRA-ST


REV -
DATE: 2/5/2026

- NOTES:
- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL
SUPPORT DRAWING
- 6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- 8. * - APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING PIPING




[]

FACE A



FACE B
PLAN VIEW



FACE A

**SHIPPING
WEIGHT**

17400 lbs+ [7895] kg+

**OPERATING
WEIGHT**

24660 lbs+ [11190] kg+

HEAVIEST SECTION WEIGHT

13180 lbs+ [5980] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY

AWT