

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

MODEL #	U-EJETME2-19106F0200F1LA
---------	--------------------------

DWG. # UEJETM2-SE-16,18

DATE	9/14/2025
------	-----------



Technical drawing of the front view of a device. The drawing shows two circular fans with a grid pattern, mounted on a rectangular frame. The dimensions are as follows:

- Overall width: $126 \frac{3}{8}$
- Distance from left edge to first fan center: 6
- Distance between fan centers: 42 (indicated by two arrows, each labeled $* 42$)
- Distance from second fan center to right edge: $36 \frac{3}{8}$
- Distance from left edge to first fan center (bottom): 4
- Distance between fan centers (bottom): 42 (indicated by two arrows, each labeled 42)
- Distance from second fan center to right edge (bottom): $38 \frac{5}{8}$

2" MPT
DRAIN

- 1) * = HANGER HOLE LOCATION.
- 2) RIGHT HAND MODEL SHOWN.
- 3) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 4) WATER DEFROST ADDS 1 3/4" INCHES TO HEIGHT OF STANDARD UNIT AND CHANGES DRAIN SIZE.
- 5) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.
- 6) **= HEIGHT OF SUCTION HEADER AND INSTALLED THERMOWELL FITTING ABOVE CABINET. CUSTOMER IS RESPONSIBLE TO ACCOUNT FOR ADDITIONAL HEIGHT NECESSARY FOR RTD AND ACCESS.



ROOM

1290 lbs+ [590] kg+

1580 lbs+ [720] kg+