

UNIT	CLOSED CIRCUIT COOLER
MODEL #	ESW4 9-44J18-SP

EVAPCO, INC.




DWG. # WX409184808P-DRA-ST


REV -
SERIAL #
DATE: 2/7/2026

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
9. COIL CONNECTIONS LOCATED ON FACES B AND D




FACE B



FACE B
PLAN VIEW



FACE A



FACE A

SHIPPING
WEIGHT

20730 lbs+ [9405] kg+

OPERATING
WEIGHT

29370 lbs+ [13325] kg+

HEAVIEST SECTION
WEIGHT

13380 lbs+ [6070] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: AWT