

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

MODEL #	U-EJETME2-21106F0100F1LA
---------	--------------------------

DWG. # UEJETM2-SE-16,18

DATE	9/16/2025
------	-----------



Technical drawing of the front view of a device. The drawing shows two circular fans with a radial grille pattern. The overall width is 126 3/8. The distance between the centers of the fans is 42. The distance from the left edge to the center of the first fan is 42. The distance from the center of the second fan to the right edge is 36 3/8. The distance from the left edge to the center of the first fan is 6. The distance from the center of the second fan to the right edge is 38 5/8. The distance between the fans is 42. The distance from the left edge to the center of the first fan is 42. The distance from the center of the second fan to the right edge is 38 5/8.

- 2" MPT
DRAIN

- 1) * = HANGER HOLE LOCATION.
- 2) RIGHT HAND MODEL SHOWN.
- 3) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 4) WATER DEFROST ADDS 1 3/4" INCHES TO HEIGHT OF STANDARD UNIT AND CHANGES DRAIN SIZE.
- 5) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.
- 6) **= HEIGHT OF SUCTION HEADER AND INSTALLED THERMOWELL FITTING ABOVE CABINET. CUSTOMER IS RESPONSIBLE TO ACCOUNT FOR ADDITIONAL HEIGHT NECESSARY FOR RTD AND ACCESS.



ROOM

1300 lbs+ [590] kg+

1620 lbs+ [735] kg+