

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

CUSTOMER

MODEL #

U-EJETME3-3286F0075F1LA

SCALE


N.T.S.

DWG. #

UEJETM3-SE-16,18

REV. 0


DATE	11/22/2025
------	------------



- NEMA 4X
JUNCTION BOX

NOTES:

- 1) * = HANGER HOLE LOCATION.
- 2) RIGHT HAND MODEL SHOWN.
- 3) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 4) WATER DEFROST ADDS 1 3/4" INCHES TO HEIGHT OF STANDARD UNIT AND CHANGES DRAIN SIZE.
- 5) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.
- 6) **= HEIGHT OF SUCTION HEADER AND INSTALLED THERMOWELL FITTING ABOVE CABINET. CUSTOMER IS RESPONSIBLE TO ACCOUNT FOR ADDITIONAL HEIGHT NECESSARY FOR RTD AND ACCESS.



Technical drawing of a vertical riser assembly. The drawing shows a cross-section of the assembly with various dimensions and labels. The top dimension is 45 3/8. Below it, the distance from the left wall to the center of the riser is 41 3/8, with a 3/4 inch offset on each side. The riser itself has a diameter of 4 7/8 inches. The distance from the top of the riser to the center of the horizontal pipe is 9 1/4 inches, marked with **. The total height of the riser is 57 1/2 inches. The distance from the bottom of the riser to the center of the horizontal pipe is 62 3/4 inches. The horizontal pipe has a diameter of 2 inches MPT. The distance from the left wall to the center of the horizontal pipe is 55 inches, with 1 1/4 inch offsets on each side. The total width of the assembly is 57 1/2 inches. An arrow labeled "AIR FLOW" points to the left. A label "2" MPT DRAIN" points to the horizontal pipe. A label "BOX" is at the top left.

PROJECT

ROOM

SHIPPING
WEIGHT

1670 lbs+ [760] kg+

OPERATING WEIGHT	10,000
------------------	--------

2050 lbs+ [930] kg+