

UNIT	CLOSED CIRCUIT COOLER
MODEL #	ESW4 9-36I12-SP

EVAPCO, INC.




DWG. # **WX409123612P-DRA-ST**

REV **-**
SERIAL #
DATE: **2/10/2026**

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING



FACE B


PLAN VIEW

FACE C



FACE D

FACE A



FACE A

SHIPPING
WEIGHT

16840 lbs+ [7640] kg+

OPERATING
WEIGHT

24100 lbs+ [10935] kg+

HEAVIEST SECTION
WEIGHT

13130 lbs+ [5955] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT