


UNIT	CLOSED CIRCUIT COOLER
MODEL #	LSWE 10-3K18

EVAPCO, INC.




DWG. #	WLE051206-DRE-RS	REV.	-
SERIAL #		DATE	3/28/2024


NOTES:
 1. (M) - FAN MOTOR LOCATION
 2. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
 3. +UNIT WEIGHT DOES NOT INCLUDE
 ACCESSORIES (SEE ACCESSORY DRAWINGS)
 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
 RECOMMENDED STEEL SUPPORT DRAWING
 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN
 [METRIC] [mm]
 6. * - APPROXIMATE DIMENSIONS DO NOT
 USE FOR PRE-FABRICATION OF CONNECTING PIPING
 7. HEAVIEST SECTION IS COIL SECTION
 8. THE SPRAY PUMP SHOULD BE SIZED FOR
 345 gpm [26.1 l/s] AND 2.0 psi [13.7 kPa]
 AT THE INLET CONNECTION(S)



PLAN VIEW



FACE D



FACE A