CLOSED CIRCUIT COOLER			EVAPCO,	TNC	evapco	DWG.# WX409184810P-DRA-S	
MODEL #	ESW4 9-45K18-LP	SCALE NTS	LVAPCO			SERIAL#	DATE: 11/25/2025
2. HÉAVIE 3. MPT DE FPT DEI BFW DE GVD DE FLG DEI 4. +UNIT V ACCESS 5. 3/4" [19N REFER SUPPOI 6. MAKE-U 20 psi M	N MOTOR LOCATION ST SECTION IS COIL SEC NOTES MALE PIPE THRE NOTES FEMALE PIPE TH ENOTES BEVELED FOR W NOTES GROOVED NOTES FLANGE VEIGHT DOES NOT INCLU BORIES (SEE ACCESSOF MM] DIA. MOUNTING HOL TO RECOMMENDED STE RT DRAWING IP WATER PRESSURE IN [137 kPa], 50 psi MAX [SIONS LISTED AS FOLLO	EAD READ VELDING JDE RY DRAWINGS) ES. EL	(2) 4" [100] BFW	FACE B PLAN VIEW (2) 4" [100] BFW FLUID OUT	(M)	CE C	FACE D
[MET 8. * - APPF FOR PR	LISH FT-IN RIC] [mm] ROXIMATE DIMENSIONS E-FABRICATION OF CON	INECTING PIPING		* 2'-10 1/2" [876]	FAC	CE A	
9. COIL CC	NNECTIONS LOCATED (T	ON FACES B AND		* 2'-2 3/8" [670]	F	F	71'-0 7/8" [327]
	(M)		* 2'-8" [813] FACE B & D COIL CONNECTI	_* 2'-10 3/4" [883]	F(M) ACCESS (DOOR)	L _(M) ACCESS DOOR	9'-3 1/4" [2826]
	2" [50] MPT — MAKE-UP 2" [50] MPT — DRAIN	0	3" [80] MPT OVERFLOW	(2)1/2" [15] FPT			19'-4 7/8" [5917] 10'-1 5/8" [3090]
2	'-3" [686]						
	3 3/8" [86] 4 1/4" [107] 5 1/4" [132]	- - 8'-5 1/2"	2'-5 5/8" [752]	2'-2 1/4" [667]		-0" 86] CE A	
FACE B							
SHIPPING WEIGHT	22990 lbs+ [10430] k		32230 lbs+ [14620] kg+	HEAVIEST SECTION WEIGHT	15430 lbs+ [7000] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT