

UNIT CLOSED CIRCUIT COOLER  
MODEL # ESW4 9-46H12-SP SCALE NTS


EVAPCO, INC.



DWG. # WX409124812P-DRA-ST


REV -  
SERIAL # DATE: 1/20/2026

NOTES:  
 1. (M)- FAN MOTOR LOCATION  
 2. HEAVIEST SECTION IS COIL SECTION  
 3. MPT DENOTES MALE PIPE THREAD  
 FPT DENOTES FEMALE PIPE THREAD  
 BFW DENOTES BEVELED FOR WELDING  
 GVD DENOTES GROOVED  
 FLG DENOTES FLANGE  
 4. +UNIT WEIGHT DOES NOT INCLUDE  
 ACCESSORIES (SEE ACCESSORY DRAWINGS)  
 5. 3/4" [19MM] DIA. MOUNTING HOLES.  
 REFER TO RECOMMENDED STEEL  
 SUPPORT DRAWING  
 6. MAKE-UP WATER PRESSURE  
 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]  
 7. DIMENSIONS LISTED AS FOLLOWS:  
 ENGLISH FT-IN  
 [METRIC] [mm]  
 8. \* - APPROXIMATE DIMENSIONS DO NOT USE  
 FOR PRE-FABRICATION OF CONNECTING PIPING




FACE B  
PLAN VIEW

FACE C



FACE D



FACE A

SHIPPING  
WEIGHT

17210 lbs+ [7810] kg+

OPERATING  
WEIGHT

24470 lbs+ [11100] kg+

HEAVIEST SECTION  
WEIGHT

13140 lbs+ [5960] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT