

UNIT	CLOSED CIRCUIT COOLER
MODEL #	ESW4 9-45I18-SP

EVAPCO, INC.



DWG. # WX409184810P-DRA-ST

REV -

SERIAL #


DATE: 2/6/2026

NOTES:

- (M) FAN MOTOR LOCATION
- HEAVIEST SECTION IS COIL SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

9. COIL CONNECTIONS LOCATED ON FACES B AND D



FACE B

(2) 4" [100] BFW
FLUID IN


FACE B
PLAN VIEW

(2) 4" [100] BFW
FLUID OUT

FACE B & D
COIL CONNECTIONS

* 2'-8" [813] * 2'-10 3/4" [883]

(2) 1/2" [15] FPT
VENT



1' 0 7/8" [327]

9' 3 1/4" [2826]

19' 4 7/8" [5917]

10' 1 5/8" [3090]

2' 2 1/4" [667] 18' 0" [5486]

FACE A

SHIPPING
WEIGHT

22300 lbs+ [10120] kg+

OPERATING
WEIGHT

31540 lbs+ [14310] kg+

HEAVIEST SECTION
WEIGHT

15220 lbs+ [6905] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: AWT