


UNIT	COOLING TOWER
MODEL #	AT 19-4L11

DWG. #	T3091148-DRD-ST	REV.
SERIAL #		DATE 2/14/2026


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
4. FPT DENOTES FEMALE PIPE THREAD
5. BFW DENOTES BEVELED FOR WELDING
6. GVD DENOTES GROOVED
7. FLG DENOTES FLANGE
8. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
9. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
10. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
11. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]




FACE B

PLAN VIEW



FACE A



FACE A