INIT	COOLING TOWER		EVADOO IN	evapco	DWG. # T4284848-DRA-ST	REV.
10DEL #	AT 428-4Q48	SCALE NTS	EVAPCO, IN	C.	SERIAL #	DATE _{12/15/2025}
2. HÉAV 3. MPT L FPT D BFW L GVD L FLG D PE DE 4. +UNIT ACCE 5. MAKE 20 psi 6. 3/4" [1 RECO 7. DIMEN [8. PAN F EVAPP BY OT 9. PAN E	AN MOTOR LOCATION JEST SECTION IS UPPER SIDENOTES MALE PIPE THRE DENOTES FEMALE PIPE THRE DENOTES BEVELED FOR WITH DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END TWEIGHT DOES NOT INCLL SSORIES (SEE ACCESSOR END WATER PRESSURE MIN [137 kPa], 50 psi MAX [3] MMM] DIA. MOUNTING HOLD MENDED STEEL SUPPORT NOINS LISTED AS FOLLOV ENGLISH FT-IN [METRIC] MM FLUME BOX EQUALIZERS SI CO. PAN EQUALIZER PIPING THERS. EQUALIZER NIPPLE IS 11'-10 EACH STEP SIDE.	EAD READ READ VELDING UDE RY DRAWINGS) 344 kPa] LES. REFER TO T DRAWING. WS: SUPPLIED BY IG IS SUPPLIED	FACE PLAN VIEV	B V	ACE C (4) ACCESS DOOR ACE A	FACE D
			7" [178]		ACE A	
2" 51]	(4) 14" [350] BFW/GVD OUTLET (4) 4" [100] MPT OVERFLOW (4) 3" [80] MPT MAKE-UP (4) 4" [100] MPT DRAIN 5 1/8" [130] 28'-3 5, [8626 FACE		11'-2 1/4" [3410] - [51]		(4) 12" [300] BRW/GVD EQUALIZER (SEE NOTE #9) 3'-7" [1092] 51'-1" 5570] ACE A	1 1/2"
SHIPPING WEIGHT	78800 lbs+ [357	745] kg+ OPE	RATING 142200 lbs+ [64505] kg+	AVIEST SECTION 13660 lbs+ [6200] kg+	NO. OF SHIPPING SECTIONS 8	RAWN BY: MER