UNIT **COOLING TOWER** SCALE NTS MODEL # AT 14-2F6

EVAPCO, INC. Evapeo





DWG. # REV. T3040624-DRJ-ST DATE 11/12/2025 SERIAL #


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]









CLITODING		ODEDATING		LIE IN GEOT OF COTTON		NO OF CHIRDING SECTIONS		DD AWN BV:
SHIPPING	1390 lbs+ [635] ka+	OPERATING	2410 lbs+ [1095] ka+	HEAVIEST SECTION	950 lbs+ [435] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY: KWC
WEIGHT	1000 ib3+ [000] kg+	WEIGHT	2410 lb3+ [1030] kg+	WEIGHT	330 ib3+ [1 33] kg+		_	KWC