UNIT	COOLING TOWER	
MODEL #	AT 14-3F12	SCALE NTS


EVAPCO, INC. EVAPCO

NG. #	T3041236-DRJ-ST	REV.
RIAL #		DATE _{11/12/2025}


NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 3/4" [19MM] DIA. MÖUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]

FACE B PLAN VIEW



FACE A





SHIPPING WEIGHT 2730 lbs+ [1240] kg+ OPERATING WEIGHT 4850 lbs+ [2200] kg+ HEAVIEST SECTION WEIGHT 1970 lbs+ [895] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: KWC