UNIT COOLING TOWER		WER
MODEL #	AT 112-2I12	SCALE NTS

EVAPCO, INC. Evapeo



DWG. # REV. T3121224-DRD-ST DATE_{12/14/2025} SERIAL #

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]


FACE C


FACE B PLAN VIEW



FACE D

FACE A





DRAWN BY: KDS NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 7330 lbs+ [3325] kg+ 4930 lbs+ [2240] kg+ 13540 lbs+ [6145] kg+ WEIGHT WEIGHT WEIGHT