
UNIT	CONDENSER	
MODEL #	eco-ATC-478A	SCALE NTS


EVAPCO, INC. Evapco




DWG. # REV. EG091410-DRC-ST DATE_{12/14/2025} SERIAL #

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]







DRAWN BY: JLG NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 18790 lbs+ [8525] kg+ 16710 lbs+ [7580] kg+ 23780 lbs+ [10790] kg+ WEIGHT WEIGHT WEIGHT