

UNIT	CONDENSER	
MODEL #	ATC-2040E	SCALE NTS

EVAPCO, INC.



DWG. # C4242410-DRA-ST


REV -

NOTES

NOTES


1. (M)- FAN MOTOR LOCATION
2. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
3. BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]

FACE B
PLAN VIEW




FACE B

FACE C



FACE D

FACE A (4) ACCESS DOOR



This architectural drawing shows a cross-section of a building. The top portion features a double-height space with two sets of doors labeled 'ACCESS DOOR (M)'. The bottom portion shows a corridor with a door on the left and a series of hexagonal panels on the right. A vertical dimension line indicates a height of 1'-3 1/4" [387] from the floor to the top of the access doors. A horizontal dimension line at the bottom indicates a total width of 24'-1 3/4" [7360] for the double-height space, with a side room having a width of 2'-10 3/8" [873].

FACE A

SHIPPING WEIGHT 77480 lbs+ [35145] kg+ OPERATING WEIGHT 103570 lbs+ [46980] kg+ HEAVIEST SECTION WEIGHT 31920 lbs+ [14480] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: JLG