NIT CONDENSER		TNC evapco	DWG. # CEWR123614-DRA-ST	REV -
ODEL# PMRC-1811 SCALE NT	EVAPCO, I	INC. evapeo	SERIAL#	DATE: 11/27/2025
NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.	FACE B PLAN VIEW	FACE C		FACE D
		FACE A		
3'-0 7/8" * 5'-8 5/8" * [1743]				
O O O O O O O O O O O O O O O O O O O	3'-11 3/4" [1213] * 7'-2 5/8" [2200]			
3"[80] MPT	9'-11" [3023] * 8'-6 3/8" [2600]			
1'-8" [508] 3 7/8" [98] 	1' 9"	36'-2" [11024]		1'-6 1/4" [464]
[3616] FACE A FACE A				
SHIPPING 74710 lbs+ [33890] kg+	OPERATING	HEAVIEST SECTION 29260 lbs+ [13275] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY: JLG
WEIGHI L TTT J	WEIGHI	WEIGHT E - 1 5		