				Lagy
CONDENSER	EVAPCO, INC. EVEPCO		CEWR12C2410-DRB-ST	REV -
PMRC-954 SCALE NTS	T LVAPCO, I		SERIAL #	DATE: 11/25/2025
NOTES:  1. (M)- FAN MOTOR LOCATION.  2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES SEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES FLANGE PE DENOTES PLAIN END  3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).  4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.  5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.  6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]  7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.	FACE E		CE C	FACE D
3'-0 7/8" * 5'-8 5/8" [937]	O REFRIG IN  4'-0 3/4" [1238] * 7'-2 5/8" [2199  0 15'-9" [4800]  9'-11" [3023] * 8'-6 3/8" [2600  2'-11 1/2" [902]- 3"[80] MPT OVERFLOW			
FACE B				
HIPPING 20160 lbc : [17765] kg : OF	<del>_</del>	HEAVIEST SECTION WEIGHT 28300 lbs+ [12840] kg+		DRAWN BY: JLG

SHIPPING WEIGHT