NIT CONDENCED		The state of the s	DWG.#	REV
CONDENSER IODEL # SCAL	=	EVAPCO, INC. Evapeo	CEWRTM2406-DRA-ST	- DATE:
PMRC-735	NTS		GERMAL #	11/27/2025
NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES FLANGE PE DENOTES FLANGE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING	G.	FACE B PLAN VIEW	FACE A	FACE D
2'-6 3/8" * [772] OVERSIZED ACCESS DOORS 2"[50] MPT MAKE UP 3"[80] MPT DRAIN 1'-8" [508] 4 3/4" [121] 5 1/8" [130] 3'-10 1/2" [1181]	3"[80] MPT OVERFLOW 9'-9 3/4" [2991]	1'-10 1/4" [565] * 5'-1 1/8" [1553] 9'-11" [3023] * 8'-6 3/8" [2600] 1'-7 1/8" 24 [486]	-0 7/8"	1'-6" [457]
SHIDDING	FACE B		NO. OF SHIPPING SECTIONS	DRAWN BY: II G
SHIPPING WEIGHT 26410 lbs+ [11980] kg+	OPERATING WEIGHT	34180 lbs+ [15505] kg+ HEAVIEST SECTION 9830 lbs+ [4460] kg+	NO. OF SHIPPING SECTIONS 3	DRAWN BY: JLG